



OP-Q

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Limit Sw itches](#) : [MICRO SWITCH™ Global Limit Sw itches](#) : [OP](#))

Enclosed Switch Series OP: Top Plunger, 1NO 1NC, SPDT

Image Not Available

Actual product
appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	13,3 N [3 lb] max.
Release Force	0.75 lb min.
Pretravel (PT)	1,98 mm [0.078 in] max.
Overtravel (OT)	4,78 mm [0.188 in] min.
Differential Travel (DT)	0,10 mm [0.004 in] max.
Product Type	Enclosed Sw itches
Actuator	Top Plunger
Lever Type	None
Circuitry	SPDT
Ampere Rating	15 A
Supply Voltage	125 Vac, 250 Vac, 480 Vac
Housing Material	Aluminum Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Series Name	OP
Sealing	NEMA 1, 3, 4, 13
UL File #	E12252
Comment	In-line actuation
Agency Approvals and Standards	UL, CSA
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Sw itches