


# RUGGED RELIABLE MICRO SOCKETS

(1.00 mm) .0394" PITCH • CLM/MLE SERIES



## CLM

**Mates:**  
FTM, FTMH, MW

## MLE

**Mates:**  
FTM, FTMH, MW

### SPECIFICATIONS

**Insulator Material:** Black LCP  
**Contact Material:**  
 CLM: Phosphor Bronze  
 MLE: BeCu  
**Plating:**  
 CLM: Au or Sn over  
 50 μ" (1.27 μm) Ni  
 MLE: Au over 10 μ" (0.25 μm) Ni  
**Current Rating (CLM/FTM):**  
 3.1 A per pin  
 (2 pins powered)  
**Current Rating (MLE/FTM):**  
 2.9 A per pin (2 pins powered)  
**Operating Temp Range:**  
 -55 °C to +125 °C  
**Max Cycles:**  
 CLM: 100 with 10 μ" (0.25 μm) Au  
**Voltage Rating:**  
 CLM: 270 VAC  
 MLE: 310 VAC  
**Insertion Depth:**  
 CLM:  
 Top Entry = (1.40 mm) .055" min.,  
 Bottom Entry =  
 (2.41 mm) .095" min.  
 (Add board thickness for  
 correct post OAL)  
 MLE:  
 (1.63 mm) .064" to  
 (3.18 mm) .125" with  
 (0.38 mm) .015" wipe,  
 pass-through, or (2.44 mm) .096"  
 minimum for bottom entry

### PROCESSING

**Lead-Free Solderable:**  
 Yes  
**SMT Lead Coplanarity:**  
 (0.10 mm) .004" max (02-25)  
 (0.15 mm) .006" max (26-50)\*  
 \*(.004" stencil solution  
 may be available; contact  
 ipg@samtec.com)

### ALSO AVAILABLE

MOQ Required

Alignment pin  
 Other Gold plating options



**Note:**  
 Some lengths, styles and  
 options are non-standard,  
 non-returnable.



02 thru 50

**-F**  
 = Gold flash on  
 contact,  
 Matte Tin on tail

**-L**  
 = 10 μ" (0.25 μm)  
 Gold on contact,  
 Matte Tin on tail

**-BE**  
 = Bottom Entry  
 (Required for bottom entry)

**-K**  
 = (3.50 mm) .138" DIA  
 Polyimide film  
 Pick & Place Pad  
 (7 positions minimum)

**-P**  
 = Pick & Place Pad  
 (7 positions minimum)




**-PA**  
 = Pick & Place Pad with  
 integral Alignment Pin

**-TR**  
 = Tape & Reel

**-FR**  
 = Full Reel Tape & Reel  
 (must order maximum  
 quantity per reel;  
 contact Samtec for  
 quantity breaks)



PIN/ROW	A
04-15	(3.56) .140
16-50	(7.11) .280



02 thru 50

**-G**  
 = 10 μ"  
 (0.25 μm)  
 Gold

**-A**  
 = Alignment Pin  
 (3 positions minimum)  
 Metal or plastic  
 at Samtec discretion

**-K**  
 = (4.00 mm) .1575" DIA  
 Polyimide film  
 Pick & Place Pad  
 (5 positions minimum)

**-P**  
 = Metal Pick & Place Pad  
 (5 positions minimum)

**-TR**  
 = Tape & Reel

**-FR**  
 = Full Reel Tape & Reel  
 (must order maximum  
 quantity per reel;  
 contact Samtec for  
 quantity breaks)

