


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		D1	REVISED PER ECO-11-004835	11MAR11	RK	HMR



D




TERMINATED VIEW

- 1
- 2
- 3
- 4
- UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
- PHOSPHOR BRONZE PER QQ-B-750.
- PLATED WITH .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000015 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.

C



DETAIL Z
SCALE 10:1
TYPICAL



OBSOLETE

3.100	3.380	3.150	63	64	1-1658620-2
2.900	3.180	2.950	59	60	1-1658620-1
2.400	2.680	2.450	49	50	1-1658620-0
1.900	2.180	1.950	39	40	1658620-9
1.600	1.880	1.650	33	34	1658620-8
1.400	1.680	1.450	29	30	1658620-7
1.200	1.480	1.250	25	26	1658620-6
1.100	1.380	1.150	23	24	1658620-5
.900	1.180	.950	19	20	1658620-4
.700	.980	.750	15	16	1658620-3
.600	.880	.650	13	14	1658620-2
.400	.680	.450	9	10	1658620-1
D	C	B	A	NO OF POSN	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± 5°

MATERIAL

1 2 3

DWN R. SAMICK 22AUG03
CHK C. ROHDE 22AUG03
APVD M. WALMSLEY 22AUG03

PRODUCT SPEC

108-40000

APPLICATION SPEC

114-40005

WEIGHT -

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 of 1

REV D1

TE Connectivity

RECEPTACLE ASSY, MILITARY POLARIZATION, LEAD FREE, AMP-LATCH™ NOVO

SIZE A2

CAGE CODE 00779

DRAWING NO C=1658620

RESTRICTED TO -