


DWG. NO.

| SYM | DCN NO. | DESCRIPTION | DATE | DRAWN | CHECKED | APP' D | APP' D |
|-----|---------|-------------|------|-------|---------|--------|--------|
|     |         |             |      |       |         |        |        |
|     |         |             |      |       |         |        |        |
|     |         |             |      |       |         |        |        |




| DESCRIPTION      | APPLICABLE WIRE |                         | AWG#<br>MARK |
|------------------|-----------------|-------------------------|--------------|
|                  | WIRE SIZE       | OUTER DIA. OF INSUL.    |              |
| D02-22-22P-10000 | AWG#22~24       | 1.3 <sup>DIA</sup> MAX. | 22           |
| D02-22-26P-10000 | AWG#26~28       | 1.1 <sup>DIA</sup> MAX. | 26           |

NOTE 1. CONTACT TO BE SUPPLIED IN REELED FORM.

(10,000 CONTACT/REEL)

2. NUMBER OF CONTACTS TO BE SHOWN ON THIS PORTION.

3. LABEL SHOWING PART NUMBER & Q'TY TO BE PUT ON THIS PORTION.



| 3                  | PIN CONTACT | 10000         | COPPER ALLOY               | GOLD OVER NICKEL                            |         |
|--------------------|-------------|---------------|----------------------------|---------------------------------------------|---------|
| 2                  | PAPER TAPE  | 1             | PAPER                      |                                             |         |
| 1                  | MAGAZINE    | 1             | PAPER                      |                                             |         |
| ITEM               | DESCRIPTION | Q'TY          | MATERIAL                   | FINISH                                      | REMARKS |
| REFERENCE DOCUMENT |             | DATE          | SCALE                      | JAE-CONNECTOR.COM                           |         |
| JACS-3050-2        |             | 9 . JUN. ' 87 | 10/1                       | JAE VIBRATION ELECTRONICS<br>INDUSTRY, LTD. |         |
| MATERIAL           |             | DRAWN         | Reference Only             |                                             |         |
|                    |             | E. MURANO     | JAE                        |                                             |         |
|                    |             | CHECKED       | NAKAGAMI-CHO, AKISHIMA-SHI |                                             |         |
|                    |             | Y. HAYASHI    | TOKYO, JAPAN               |                                             |         |
| TREATMENT          |             | APP'D         | DWG. NO.                   |                                             |         |
|                    |             | K. Takeuchi   | SJ021507-E                 |                                             |         |
| FINISH             |             | APP'D         |                            |                                             |         |
|                    |             | S. Ishimoto   |                            |                                             |         |

|                               |                        |
|-------------------------------|------------------------|
| DIMENSIONS ARE IN MILLIMETERS |                        |
| TOLERANCES ON: (INCHES)       |                        |
| <u>DIMENSION</u>              | <u>ANGLES</u>          |
| . ± 0.3                       | X° ±                   |
| .X ± 0.3                      | X°X' ±                 |
| .XX ±                         |                        |
| .XXX ±                        | <u>CONCENTRICITY</u>   |
|                               | <u>WITHIN</u> T. I. R. |