

	1	2	3	4	5	6	7	8	
F					REV.	ECN NO.	DATE	SIGN	DESCRIPTION
					B	C200383	2020-03-28	Peng	△BXI
E									
D									
C									
B									
A									

SAFI2C-XXG03

△B

01:MPQ(1000PCS)/REEL
02:LOOSE PIECE 500PCS
03:LOOSE PIECE 100PCS

4.3

4.0

SECTION A-A

R4.0

SECTION B-B

Ø 3.50

Ø 4.00

22.1 (REF)

14.50

3.00

Note:

- * Material
 - Contact Body: Copper Alloy
 - Outer Spring: Stainless steel
- * Contact Finish: 3u"Min Gold Plating
- * Current Rating: 20A Max
- * Termination Type: Crimping
- * Wire Range: 14AWG~12AWG
- * Salt Spray Test 48H
- * This drawing is supplied for information only design features specifications and performance data

UNIT:mm			TITLE		
TOLERANCE			20A FEMALE CLAW PIN TERMINAL		
			SCALE	SIZE	SHEET
			3:1	A4	1
±0.5			REV.	WC-REV.	QC
			B	A.3	Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
SAFI2C-XXG03	Jinhai	2015-08-12
ALTW	Rensong	2015-08-12
	Jerry	2015-08-12

W10814-03-0001A2