




RoHs

2.50 ± 0.10 (PITCH)

DIMA ± 0.20

DIMB ± 0.25

2 Pin样式

SECTION A-A

5.75 ± 0.25

3.40 ± 0.20

7.00 ± 0.25

0.64 ± 0.05

DIMA ± 0.10


2.50

Ø0.90

适用线路板 (PCB LAYOUT)

序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 直针 端子	Copper Alloy/ Tin Plating

Technical Index:
1. Temperature range: -25° C~85° C.
2. Rated voltage: 250VDC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: ≤20mΩ.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: ≥1000MΩ.

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
X.° ±0.50	X.° ±5°	PART NO. W2542110-XPR2123		TITLE: XH2.5 直针
X.X° ±0.20	X.X° ±3°	DESIGN: James	CUSTOMER	SIZE A4
X.XX° ±0.10	X.XX° ±1°			UNITS MM
MANUFACTURE DWG		CHED: Talen		SCALE N:A
		APPD: Sophia		SHEET 1/1