

6

5

4

3




2

1

used for: D-SUB HD

AT ALL TIMES WATER RESISTANT CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD.

No. of pos.	A ^{+0.2}	B ^{+0.2}	C	D ^{-0.25}	Part-No.
15	21.1	39.4	25.00 ^{+0.12} _{-0.13}	16.46	6HDD15SCR99E20X
26	21.1	47.7	33.30 ^{+0.15} _{-0.1}	24.79	6HDD26SCR99E20X
44	21.1	61.4	47.04 ^{±0.13}	38.50	6HDD44SCR99E20X
62	21.1	77.9	63.50 ^{±0.13}	54.96	6HDD62SCR99E20X



NOTES:

- METAL SHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING MATING AREA: 30µin HARD GOLD OVER min. 50µin NICKEL
- THREADED SPACER CLIP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: $\phi 3.1 \pm 0.1$; PCB THICKNESS 1.6mm
- COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- FRAME: ZINC DIE CAST ; NICKEL PLATED
- HEXLOCKING SCREW: STAINLESS STEEL
- P.C.B. HOLE DRILLINGS ON SHEET 2
- RECOMMENDED TORQUE FOR MOUNTING SCREW 35N cm (3.1 in.LB) / max. 40N cm (3.5 in.LB)
- CONNECTOR IS PART MARKED: **PART-NO. CONEC ABC**

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

tolerance				dim. in mm	
2006	date	name	2006	date	name
drawn	15.08.	Lehmenkühler	drawn	15.08.	Lehmenkühler
appd.	15.08.	Mickenbecker	appd.	15.08.	Mickenbecker
norm	DIN 41652				
d-old					
a	Origin				
rev.	description	date	name		

CONEC

scale: 2:1	material: SEE NOTES
title: D-SUB HD FEMALE 15-62pos. SOLDER PIN STRAIGHT with threaded spacer clip	
dwg no: AutoCAD 2006	DIN-A 3
part no: SEE TABLE	

6


5

4


2

1


used for: D-SUB HD




15 pos.



26 pos.



44pos.



62pos.

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

tolerance				dim. in mm	
2006	date	name	2006	date	name
drawn	15.08.	Lehmenkühler	drawn	15.08.	Lehmenkühler
appd.	15.08.	Mickenbecker	appd.	15.08.	Mickenbecker
norm	DIN 41652		norm	DIN 41652	
d-old			d-old		
a	Origin		a	Origin	
rev.	description	date	rev.	description	date

CONEC

scale: 2:1	material: SEE SHEET 1
title: P.C.B. HOLE DRILLINGS	
D-SUB HD FEMALE 15-62pos. SOLDER PIN with threaded spacer clip	
dwg no: AutoCAD 2006	DIN-A 3
18K2A448	
part no: SEE SHEET 1	