




3

2

1



B

B

A

A

注 記

- 1. 対応合機品番 : 7182-1495 ETC., 7182-1497 ETC., 7282-1020 ETC.
- 2. 適用端子品番 : 7116-4020 ETC.

NOTES

- 1. MATING PART NO. : 7182-1495 ETC., 7182-1497 ETC., 7282-1020 ETC.
- 2. APPLICABLE TERMINAL NO. : 7116-4020 ETC.

PART NO. AND CH. CODE	COLOR
7183-1495, ☒	NATURAL
7183-1495-30, ☒	BLACK
7183-1495-40, ☒	LIGHT GRAY
7183-1495-50, ☒	ORANGE
7183-1495-60, ☒	GREEN
7183-1495-90, ☒	BLUE

		CUSTOMER				MATL. SPEC.		HPA		TREAT. & FIN.		ISSUE MARK		
		CUSTOMER		PART NO.		CUSTOMER DWG NO.								
☒		10. 11. 15	CHANGED PART NAME		C10-ZB05	J. C								
☒		99. 07. 30	CORRECT ALL ERRORS		C99-M225	I. I								
☒		98. 05. 28	NEW, ☒		C98-L964	H. K	OFFICE		TRIAL PART NO.		NAME ☒ 090II 2P HOUSING FEMALE			
LET		DATE	REVISION RECORD		NO.	CHKD	VENDOR							
GENERAL TOLERANCE														
		10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT	DWG TYPE	DWG SOURCE	DWG DATE	UNIT	SCL	ANGLE
A		±0.15	±0.2	±0.3	±0.5	±0.75	±30'	0.1	R	NEW	98.05.28	mm	2/1	3
B		±0.2	±0.3	±0.55	±0.95	±1.4	±30'	0.1	APPROVED	CHECKED	CHECKED	DESIGN	DRAWN	
(C)		±0.3	±0.5	±0.8	±1.4	±2	±30'	0.15	S. MIZUSE		R. CABANGAL	AKEDA	J. CANDO	
SPECIFIED														
		MASS												
		10. 11. 15									10. 11. 15	97. 06. 06	10. 11. 15	
YAZAKI CORPORATION														

3

2

1