





RoHs



Technical Index:


1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 200V DC/AC(rms).
3. Rated current: 2.0A.
4. Contact resistance: $\leq 25\text{m}\Omega$.
5. Withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.



SECTION A-A

序号	品名	材质
1	PH2.0 直针 胶芯	PA66 UL94V-2 Yellow
2	PH2.0 直针 端子	Copper Alloy/ Tin Plating

Part No	Pin	A	B
W2001110-2PY2123	2	2.00	6.00
W2001110-3PY2123	3	4.00	8.00
W2001110-4PY2123	4	6.00	10.00
W2001110-5PY2123	5	8.00	12.00
W2001110-6PY2123	6	10.00	14.00
W2001110-7PY2123	7	12.00	16.00
W2001110-8PY2123	8	14.00	18.00
W2001110-9PY2123	9	16.00	20.00
W2001110-10PY2123	10	18.00	22.00
W2001110-11PY2123	11	20.00	24.00
W2001110-12PY2123	12	22.00	26.00
W2001110-13PY2123	13	24.00	28.00
W2001110-14PY2123	14	26.00	30.00
W2001110-15PY2123	15	28.00	32.00
W2001110-16PY2123	16	30.00	34.00
W2001110-17PY2123	17	32.00	36.00
W2001110-18PY2123	18	34.00	38.00
W2001110-19PY2123	19	36.00	40.00
W2001110-20PY2123	20	38.00	42.00



适用线路板 (PCB LAYOUT)

GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd	
X. [°] ±0.50	X. [°] ±5°	PART NO. W2001110-XPY2123	TITLE: PH2.0 直针
X.X [°] ±0.20	X.X [°] ±3°	DESIGN: James	CUSTOMER
X.XX [°] ±0.10	X.XX [°] ±1°	CHED: Talen	
MANUFACTURE DWG		APPD: Sophia	SIZE A4
			UNITS MM
			SCALE N:A
			SHEET 1/1