







RoHs

Part No	Pin	A	B
W254111K-2PY2123	2	2.5	7.5
W254111K-3PY2123	3	5.0	10.0
W254111K-4PY2123	4	7.5	12.5
W254111K-5PY2123	5	10.0	15.0
W254111K-6PY2123	6	12.5	17.5
W254111K-7PY2123	7	15.0	20.0
W254111K-8PY2123	8	17.5	22.5
W254111K-9PY2123	9	20.0	25.0
W254111K-10PY2123	10	22.5	27.5
W254111K-11PY2123	11	25.0	30.0
W254111K-12PY2123	12	27.5	32.5
W254111K-13PY2123	13	30.0	35.0
W254111K-14PY2123	14	32.5	37.5
W254111K-15PY2123	15	35.0	40.0
W254111K-16PY2123	16	37.5	42.5
W254111K-17PY2123	17	40.0	45.0



适用线路板 (PCB LAYOUT)

序号	品名	材质
1	HA2.5 胶芯	PA66 UL94V-2 Yellow
2	HA2.5 直针端子	Copper Alloy/ Tin Plating

Technical Index:

1. Temperature range: -25° C~85° C.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: ≤20m Ω.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: ≥1000M Ω.

GENERAL TOLERANCES UNLESS SPECIFIED			
X.° ±0.50	X.° ±5°	PART NO. W254111K-XPY2123	
X.X° ±0.20	X.X° ±3°	TITLE: HA2.5 直针带扣	
X.XX° ±0.10	X.XX° ±1°	DESIGN: James	CUSTOMER
MANUFACTURE DWG		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
			SCALE N:A
			SHEET 1/1