


PIN RECEPTACLES

FOR 0,64 - 0,94 DIAMETER PINS AND 0,64 SQUARE PINS

0401/6401

X401-0-15-XX-47-XX-04-0

Press-fit in 1,63 mounting hole




Basic Part Number	Length A
0401-0	8,64
6401-0	13,72

1303

1303-0-15-XX-47-XX-04-0


Press-fit in 1,55 mounting hole



8303

8303-0-15-XX-47-XX-04-0


Press-fit in 1,55 mounting hole



4095

4095-0-15-XX-47-XX-04-0

Press-fit in 1,55 mounting hole



8806


8806-0-18-XX-47-XX-40-0

Surface mount


Also available on 12mm wide carrier tape:

4,000 parts per 330mm reel

Order as: 8806-0-58-XX-47-XX-10-0



P.C.B. Layout



SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Millimeters

Tolerances On: Lengths: $\pm 0,13$
Diameters: $\pm 0,051$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - 1X - XX - 47 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

- 01** 5,08 μ m TIN/LEAD OVER NICKEL
- 80** 5,08 μ m TIN OVER NICKEL (RoHS)
- 15** 0,25 μ m GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 01** 5,08 μ m TIN/LEAD OVER NICKEL
- 80** 5,08 μ m TIN OVER NICKEL (RoHS)
- 27** 0,76 μ m GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#47 CONTACT (DATA ON PAGE 256)

(For alternate contact choices, see group D on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com