




PART NO.	"A"±.020	"B"	"C"	"D" REF	LED TYPE
SQLEDS1-4-26	.250 [6.4]	.17 [4.3]	.03 [0.8]	.17 [4.3]	T-1
SQLEDS1-6-26	.375 [9.5]				
*SQLEDS1-8-26	.500 [12.7]				
SQLEDS2-4-26	.250 [6.4]	.24 [6.4]	.07 [1.8]	.27 [6.9]	T-1 3/4
SQLEDS2-6-26	.375 [9.5]				
SQLEDS2-8-26	.500 [12.7]				
*SQLEDS2-10-26	.625 [15.9]				
SQLEDS2-12-26	.750 [19.1]				




*PARTS AVAILABLE BY SPECIAL ORDER



NOTES:

1. MATERIAL: PVC (RMS-26)
2. COLOR: BLACK.
3. ALTERNATE UNITS FOR REFERENCE ONLY

F	REDRAWN,CO 200752	SK	01/27/12
-	SEE ENGINEERING FOR REV A TO E	-	-----
REV.	DESCRIPTION	ENGR.	DATE

TITLE: SQUARE LED SPACERS						UNITS: IN [mm]	
CREATED USING SOLIDWORKS	FILE #: SQLEDS		DWN: SK	APP: SK		FINAL	
TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: A	DT: 01/27/2012	CHKD: DZ	PART #	PRINT TYPE	
RE: RICHCO, INC.		RICHCO, INC. WWW.RICHCO-INC.COM			SEE TABLE	CA	