

$A=2.0*\frac{n^P}{2}\pm0.40$
 $B=2.0*\frac{n^P}{2}-2.0\pm0.20$




Technical Data
Material:
Contact material:Brass
Plating:Gold Flash
Insulator material:Black polyester UL94V-0
Standard:6T+30%G.F

Electrical:

Current rating:1.5Amps/contact max.
Contact resistance:≤20mΩ/contact
Insulation resistance:≥1000MΩ at V=100V
Withstanding voltage:450V AC/minute

Mechanical:

Soldering temperature: +260℃, 4s max
UNSPECIFIED TOLERANCE: ±0.20



PCB Layout

APPROVALS				DATE	DEALON 德之隆® ELECTRONICS CO.,LTD			
DRAWN	G.M.Chen	2015/5/22	TITLE:		2.00mm Pin Header Connectors			
CHECKED			PART NO.		DZ200R-22-XX-44			
APPROVALS			UNIT: mm		SCALE: 1:1		SHEET 1 OF 1	
TOLERANCES ARE			30 ^{±0.15} 10 ^{±0.10} 5 ^{±0.10}	±0.30 ±0.20 ±0.15	ANGLE	±2°	DRAWING NO.	
			~ 5	±0.10			PROJ. ①	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			