




PCB Layout(Pattern Side)

Circuit Diagram

NO.1	
PART NO	vigor
1	90±30
2	130±30
3	180±30
4	250±30
5	350±50

NO.2	
Contact	MATERIAL/QTY.
S	SUS/1PC
D	SUS/2PCS

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

⑥	TERMINAL 2	—	1	Brass(0.20t)	Ag-PLATED	—
⑤	TERMINAL 1	—	1	Brass(0.20t)	Ag-PLATED	—
④	Cover	—	1	Sheet Iron	Plating Nickel	—
③	Contact	—	1	Stainless Steel	Ag-PLATED	—
②	Base	—	1	NYLON	Black	—
①	Keystoke	—	1	NYLON	Gray	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	J.X.Zhang	2015/3/18					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1107ST-A□□W-□□		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.