

OPH-AR7

Products > Switches > Limit Switches > Specialty Limit Switches > OP Series > OPH-AR7

Overview

Enclosed Switch Series OP: Side Rotary, Fixed lever length with steel roller, 1NO 1NC SPDT, CW actuation.

Honeywell MICRO SWITCH OP Series are precision, snap-action switches.

[View More](#)



Technical Specifications

Availability	Global
Release Force	4 oz min.
Overtravel (OT)	25°
Product Type	Enclosed Switches
Termination Type	0.5 in - 14NPT Conduit
Operating Force (OF)	2,22 N to 6,67 N [8 oz to 24 oz]
Pretravel (PT)	5,56 mm [0.219 in] max.
Differential Travel (DT)	0.025 in max.
Actuator	Side Rotary
Circuitry	SPDT

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
PDF PK 88008: OP switches	Installation Instructions	English	317KB
PDF MICRO SWITCH Limit Switches Comparison	Product Range Guide	English	460KB
PDF Enclosed Switches OP Series	Catalog Information	English	476KB
PDF PK 88012: EX and OP - replacement parts	Installation Instructions	English	139KB

[View More](#)

Product Features

- Cast aluminum housing
- UL, CSA
- Mounts from four sides
- Cover seal, captive cover screws
- Momentary contact
- Grounding screw
- Wide choice of actuators

Applications

- Packaging equipment
- Special machinery
- Conveyors
- Printing trades machinery

- [view all OPH-AR7 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email technical support](#)
- [start a chat](#) we're offline
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

Feedback

NAVIGATION LINKS

- HOME PAGE
- PRODUCTS
- DISTRIBUTOR INVENTORY
- INDUSTRIES
- SUPPORT
- NEWS & EVENTS
- ABOUT US

DISTRIBUTOR LINKS

- ECOM LOGIN
- LEARN CENTER
- REQUEST ACCESS TO ECOM
- SALES/AD PORTAL LOGIN
- SALES/AD PORTAL ACCESS REQUEST
- SAMPLE REQUEST
- SUPPLIER MICROSITE

LANGUAGE

-

SOCIAL MEDIA



SITE INFORMATION

- PRIVACY STATEMENT
- SITE MAP
- TERMS & CONDITIONS

