






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT

VIEWED FROM CONNECTOR SIDE



RECOMMENDED MODULE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 18MAR2013	 TE Connectivity				
		CHK SIMON LI 18MAR2013					
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.25 2 PLC ±0.15 3 PLC ±0.10 4 PLC ±. ANGLES ±. FINISH	APVD CORELI WANG 18MAR2013	NAME SOCKET ASSEMBLY DDR4 DIMM, T/H TYPE 288 POSITION				
mm		PRODUCT SPEC 108-115067					
		APPLICATION SPEC 501-115076	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -	
		MATERIAL -	WEIGHT -	A200779C-2199154			
		CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 8	REV C8

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-





SOFT TRAY	BOARD LOCK	BLUE(2935U)	BLUE(2935U)	0.00038 MIN	2.10	9-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00038 MIN	2.10	9-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	GREEN(375C)	0.00038 MIN	2.67	9-2199154-2
SOFT TRAY	BOARD LOCK	GREEN(375C)	BLACK	0.00076 MIN	2.10	8-2199154-9
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00038 MIN	2.67	8-2199154-8
SOFT TRAY	BOARD LOCK	NATURAL	YELLOW(107C)	0.00076 MIN	3.18	8-2199154-7
SOFT TRAY	BOARD LOCK	NATURAL	YELLOW(107C)	0.00038 MIN	3.18	8-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00076 MIN	3.18	8-2199154-4
SOFT TRAY	BOARD LOCK	GREEN(375C)	BLACK	0.00050 MIN	3.18	8-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLUE(2935U)	0.00038 MIN	3.18	8-2199154-2
SOFT TRAY	BOARD LOCK	GREEN(375C)	BLACK	0.00076 MIN	2.67	8-2199154-1
SOFT TRAY	BOARD LOCK	BLUE(2935U)	BLUE(2935U)	0.00038 MIN	2.67	7-2199154-9
SOFT TRAY	BOARD LOCK	NATURAL	YELLOW(107C)	0.00076 MIN	2.67	6-2199154-9
SOFT TRAY	BOARD LOCK	BLUE(2935U)	BLUE(2935U)	0.00038 MIN	3.18	6-2199154-6
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00076 MIN	3.18	6-2199154-4
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00076 MIN	3.18	6-2199154-0
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00050 MIN	3.18	5-2199154-2
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00050 MIN	3.18	5-2199154-1
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00076 MIN	3.18	2-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00038 MIN	3.18	2-2199154-5
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00038 MIN	3.18	2-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00038 MIN	3.18	2-2199154-1
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00076 MIN	2.10	1-2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00038 MIN	2.10	1-2199154-5
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00076 MIN	2.10	1-2199154-4
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00038 MIN	2.10	1-2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00076 MIN	2.10	1-2199154-2
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00038 MIN	2.10	1-2199154-1
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00076 MIN	2.67	2199154-6
SOFT TRAY	BOARD LOCK	NATURAL	NATURAL	0.00038 MIN	2.67	2199154-5
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00076 MIN	2.67	2199154-4
SOFT TRAY	BOARD LOCK	BLACK	BLACK	0.00038 MIN	2.67	2199154-3
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00076 MIN	2.67	2199154-2
SOFT TRAY	BOARD LOCK	NATURAL	BLACK	0.00038 MIN	2.67	2199154-1
PACKING STYLE	HOUSING STYLE	EXTRACTOR COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE 	DIM A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18MAR2013 RICHARD MA CHK 18MAR2013 SIMON LI APVD 18MAR2013 COREL WANG		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±1 1 PLC ±0.25 2 PLC ±0.15 3 PLC ±0.10 4 PLC ±- ANGLES ±-		NAME SOCKET ASSEMBLY DDR4 DIMM, T/H TYPE 288 POSITION	
		PRODUCT SPEC 108-115067 APPLICATION SPEC 501-115076		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL -		FINISH -		A200779 C=2199154 -	
CUSTOMER DRAWING				SCALE 1:1 SHEET 3 of 8 REV C8	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD

A1471-9 (3/11)





D

C

B


A

D

C

B

A



1. MATERIALS :
TRAY: PVC, COLOR: TRANSPARENT
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
2. DIMENSIONS:
TRAY: L=343;W=305;H=32.5
BOX: L=365;W=323;H=200
3. QUANTITY:
80 PCS/TRAY
320 PCS/BOX
4. WEIGHT:
NET WEIGHT: 1.9KG
GROSS WEIGHT: 3.4KG

SOFT TRAY PACKING

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN18MAR2013
RICHARD MA

CHK18MAR2013
SIMON LI

APVD18MAR2013
COREL WANG

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±1
1 PLC	±0.25
2 PLC	±0.15
3 PLC	±0.10
4 PLC	±
ANGLES	±
FINISH	

MATERIAL

-

18MAR2013
RICHARD MA

18MAR2013
SIMON LI

18MAR2013
COREL WANG

PRODUCT SPEC
108-115067

APPLICATION SPEC
501-115076

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
SOCKET ASSEMBLY
DDR4 DIMM,T/H TYPE
288 POSITION

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2199154

RESTRICTED TO
-

SCALE
1:1

SHEET
7

OF
8

REV
C8

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-						

D

C

B


A

D

C

B

A



1. MATERIALS :
TRAY: HIPS, COLOR: BLACK
BOX: CORRUGATED FIBERBOARD
TRANSPARENT BAG: PE
2. DIMENSIONS:
TRAY: L=326;W=136;H=28.2
BOX: L=323;W=285;H=335
3. QUANTITY:
24 PCS/TRAY
480 PCS/BOX
4. WEIGHT:
NET WEIGHT: 3.0KG
GROSS WEIGHT: 6.7KG

HARD TRAY PACKING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RICHARD MA 18MAR2013	TE Connectivity			
DIMENSIONS:		CHK SIMON LI 18MAR2013				
mm		APVD COREI WANG 18MAR2013	NAME SOCKET ASSEMBLY DDR4 DIMM,T/H TYPE 288 POSITION			
		PRODUCT SPEC	SIZE A200779			
		APPLICATION SPEC	CAGE CODE C-2199154			
MATERIAL		WEIGHT	DRAWING NO			
-		-	RESTRICTED TO			
		CUSTOMER DRAWING	SCALE 1:1			
			SHEET 8 OF 8			
			REV C8			