





NOTES:

1. METALSHELLS: STEEL; min. 315µin TIN OVER 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
4. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. ADAPTER SCREWD: COPPER ALLOY; NICKEL PLATED
6. ADAPTER HOUSING: PBT GF UL 94 V-0; BLACK
7. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
8. CONNECTOR IS PART MARKED: 163A50079X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance				 dim. in mm		scale: 2:1 (5:1)											
																material: SEE NOTES											
										DO NOT ALTER CAD DRAWING BY HAND								date		name		title: D-SUB ADAPTER 25pos. MALE / FEMALE with Adapter screws M3					
														drawn		07.03.14		Henneboel									
														appd.		10.03.14		Lehmenkühler									
				norm				dwg no: 16K1A3412																			
				d-old																							
								part no: 163A50079X																			
a				Original																							
rev.		description		date		name																					

CONEC®