




Technical Data
Material:
Contact material:Brass
Plating:Gold Flash
Insulator material:Black polyester UL94V-0
Standard:PA6T+30%G.F

Electrical:
Current rating:1.0Amps/contact max.
Contact resistance:≤20mΩ/contact
Insulation resistance:≥1000MΩ at V=100V
Withstanding voltage:300V AC/minute
Mechanical:
Soldering temperature:+260℃, 4s max
UNSPECIFIED TOLERANCE: ±0.20



A=1.27* $n_P \pm 0.40$
B=1.27* $n_P - 1.27 \pm 0.20$

APPROVALS				DATE	DRAWN				DATE
DRAWN				G.M.Chen	2015/5/22				
CHECKED					TITLE:				1.27mm Pin Header Connectors
APPROVALS					PART NO.				DZ127R-11-X-20
TOLERANCES ARE				30 ± 0.15 10 ± 0.20 5 ± 0.10 ~ 5	ANGLE				±2°
NEW					UNIT: mm				SCALE: 1:1
DESCRIPTION.				CHANGE.	CHECK.				SHEET 1 OF 1
ECN NO.				REV.	DATE.				PROJ.