




## NOTES:

### 1. MATERIAL:

ITEM 1+2+3: COPPER ALLOY

ITEM 3: NICKEL PLATED

### 2. PLATING:

ITEM 1: SEE TABLE

ITEM 2: TIN PLATED

(b)

| PLATING ITEM 1                         | PART-NO.   |
|----------------------------------------|------------|
| GOLD FLASH over NICKEL                 | 131A13049X |
| 30µin HARD GOLD over min. 50µin NICKEL | 131C13049X |


RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

| 3 x b | Ä5471       | 05.01.2015 | Heinrich |
|-------|-------------|------------|----------|
| a     | Original    |            |          |
| rev.  | description | date       | name     |

tolerance



dim. in mm

**CONEC®**

scale:

5:1

material:

SEE NOTES

title:

**HIGH POWER CONTACT MALE**  
SOLDER PIN 90°, Ø 3,75 , 40A  
D-SUB COMBINATION

dwg no:

13K1A4858

DIN-

A4

sh: 1

part no:

SEE TABLE