

[Connectors > Rectangular Connectors > Standard Rectangular Connectors](#)Product Type: **Connector Kit**Connector Style: **Receptacle**Mating Alignment: **With**Mating Alignment Type: **Keyed**Mating Retention: **With**

Features

Product Type Features

Shell Size	50.8 [2]
Boxmount	No
Housing Type	Stacking Hole
Product Type	Connector Kit
Connector Style	Receptacle
Shielded	No
Row-to-Row Spacing	2.54 mm [.1 in]
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	40
Number of Rows	2

Body Features

Plating Material	Cadmium
------------------	---------

Contact Features

Contact Type	Pin
--------------	-----

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Hardware	Jackscrew
Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Jackscrew
Contact Retention	With

Housing Features

	.099 in
--	---------

Operation/Application

Option	With Cable Clamp and With Ears On Shell
--------	---

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JUL 2017 (174)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

TE Part #244114-000
MTCPK2PJC22SSTE Part #534211-000
55A2122-22-6/9-9CS2275TE Part #218045-001
55A8040-2-5DTE Part #218047-000
55A8040-6-5DTE Part #828430-8
2X 8P AMPMODU II
STIFTLEITE Part #401927-000
D-500-0457-3-613-078TE Part #164526-000
MTCPK1RJC02PTE Part #303726-000
MTCPK2RJC22SSTE Part #446901-000
TXR41AB00-0806AITE Part #757117-000
TXR54AB00-1412BI

Documents

Product Drawings

MTCPK2RJC22PP

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_966294-000_B_c-966294-000-b.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_966294-000_B_c-966294-000-b.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_966294-000_B_c-966294-000-b.3d_stp.zip](#)

English

Product Specifications

MTC Connectors with Removable Contacts and Jackscrew Coupling Hardware

English