




RoHs

2.50 ± 0.15 (PITCH)

DIMA ± 0.25

DIMB ± 0.25

2~4P

SECTION A-A

6.37 ± 0.25

5.80 ± 0.20

7.00 ± 0.20

4.85 ± 0.20

5.70 ± 0.25

7.17 ± 0.20

0.64 ± 0.05


DIMA ± 0.10

2.50

Ø0.90

适用线路板 (PCB LAYOUT)

Technical Index:
1. Temperature range: -25° C~85° C.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: ≤20mΩ.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: ≥1000MΩ.

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd				
X.° ±0.50	X.° ±5°	PART NO. W254110K-XPR2123		TITLE: HA2.5 弯针带扣		
X.X° ±0.20	X.X° ±3°	DESIGN: James		CUSTOMER	SIZE A4	UNITS MM
X.XX° ±0.10	X.XX° ±1°	CHED: Talen			SCALE N:A	SHEET 1/1
MANUFACTURE DWG		APPD: Sophia				

序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 弯针端子	Copper Alloy/ Tin Plating