





Technical drawing of a U-shaped component. The drawing shows a top view with a central rectangular body and a flange at the top. The flange has four vertical pins or slots. The overall width is dimensioned as 1.5. The overall height is dimensioned as (42.1). A radius dimension R2 is indicated on the inner corner of the U-shape.

1 MATERIAL: STAINLESS STEEL


2 SURFACE: BLANK

3 PACKAGING 100 PIECES MAX. IN A BOX

1 MATERIAL: NICHTROSTENDER STAHL

2 OBERFLAECHE: BLANK

3 VERPACKUNG MAX. 100 TEILE IM VERSANDKARTON

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HERRMANN		20AUG2010		 TE Connectivity	
DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWEILIGS LETZTGÜLTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.		CHK M.SZELAG		20AUG2010			
DIMENSIONS: MASSEINHEITEN: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		APVD S.HEIN		NAME	
		0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ±		PRODUCT SPEC PRODUKTSPEZ.		SIDE CLIP LAENGSBUEGEL	
		ANGLES/W INKL ±°		108-94252		-	
MATERIAL		FINISH/OBERFLÄCHE/FARBE		APPLICATION SPEC VERARBEITUNGSSPEZ.		SIZE	
-1		2		114-94067		CAGE CODE	
				WEIGHT GEWICHT 14.0g		DRAWING NO. ZEICHNUNGS-NR.	
						A 3 00779 C-2120339	
				CUSTOMER DRAWING		RESTRICTED TO NUR FUER	
				/KUNDENZEICHNUNG		-	
				SCALE MASSSTAB		SHEET BLATT	
				2:1		1 OF VON 1	
						REV B1	