

M23 Cable to cable housing 3-7 mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 100 0309
Specification	M23 Cable to cable housing 3-7 mm
HARTING eCatalogue	https://b2b.harting.com/09151000309

Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Signal
Type of hood/housing	Cable to cable housing
Description of hood/housing	Rear mounting

Version

Size	M23
Locking type	Screw locking ComLock rapid locking

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	3 ... 7 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	74 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140184183
ETIM	EC003556
eCl@ss	27440224 Shell for circular connectors