







REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
1. Rated voltage: 1250V AC.DC
 2. Rated current: 2A AC DC
 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 4. Insulation resistance: $\geq 800 \text{ M}\Omega$
 5. Withstand voltage: 500V AC/minute
 6. Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : Nylon UL94V-0(2)
 8. Matched RoHS criteria


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL20024(51006)-R	TITLE: 2.00 mm Pitch Wire To Wire Housing
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:20.10.12
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DATE:20.10.12	PART NO:
FINISH: _____		CHKD:Wu Hui	SCALE: N/A
DRAWING NO:		DATE:20.10.12	PAGE: 1/1
		APPD:Ren An De	UNITS: mm
			REV. : A

REV.	REVISION DESCRIPTION	DATE	APPD


NOTES:
Rated voltage: 125V AC.DC
Rated current: 2A AC DC
Contact resistance: $\leq 20\text{ m}\Omega$
Insulation resistance: $\geq 800\text{ M}\Omega$
Withstand voltage: 500V AC/minute
Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
Wire range: AWG#28~#24
Materials:
Terminal: Phosphor bronze,Tin plated



SECTION A-A




SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL20024 (51005)-T	TITLE: 2.00 mm Pitch Wire To Wire Crimp Terminal
.XX: ± 0.15	.X° : ± 2.0°		
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:20.10.12
FINISH:		CHKD: Wu Hui	DATE:20.10.12
DRAWING NO:		APPD:Ren An De	DATE:20.10.12
		UNITS: mm	PAGE: 1/1
			REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES:
Rated voltage: 125V AC.DC
Rated current: 2A AC DC
Contact resistance: $\leq 20\text{ m}\Omega$
Insulation resistance: $\geq 800\text{ M}\Omega$
Withstand voltage: 500V AC/minute
Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
Wire range: AWG#28~#24
Materials:
Terminal: Phosphor bronze,Tin plated

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL20024(51006)-RT	TITLE: 2.00 mm Pitch Wire To Wire Crimp Terminal
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:20.10.12
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:20.10.12
FINISH:		APPD:Ren An De	DATE:20.10.12
DRAWING NO:		UNITS: mm	PAGE: 1/1 REV.: A