






P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	25MAR22	K.Z	J.Z
	B	ECN-23-219172	26JUN23	K.Z	J.Z
	B1	ECN-24-256241	14MAR24	K.Z	J.Z



(TABLE 1: PLUG)

MCP 2.8	1-968855-1	0.5-1.0	Ø1.40-2.10	828904-1	828922-1	Ø5.20
	1-968857-1	1.0-2.5	Ø2.20-3.00	828905-1	828922-1	Ø5.20
MCP 1.5K	1564324-1	0.35	Ø1.20-1.40	964971-1	1394132-1	Ø3.60
	1241380-1	0.5-1.0	Ø1.40-1.90	963530-1	1394132-1	Ø3.60
	1241380-1	0.5-1.0	Ø1.40-2.10	964972-1	1394132-1	Ø3.60
TERMINAL	TERMINAL P/N	WIRE SIZE (mm ²)	INSULATION WIRES (mm)	SWS P/N	PLIND PLUG	CAVITY DIAMETER

NOTES:

1. ASSY DELIVERED WITH LEVER IN PRE-LOCK POSITION, IF LEVER UNEXPECTED EBECOME ENGAGED, PLEASE MOVE LEVER PRE-LOCK POSITION.
2. TE ASSEMBLY P/N SEE TABLE.
3. MATING CONNECTOR: 2390416-1 OR 1743062-X
4. APPLICABLE TERMINAL PART MUNMBERS AND WIRE SIZES:SEE TABLE 1.
5. GENERAL TOLERANCE IS ± 0.3 , $\pm 3^\circ$

1	A	OGANGE	LSR3386/30	36WAY SEAL	4
1	A	GRAY	PBT-GF30	36WAY LEVER	3
1	B	BLACK	PBT-GF30	36WAY CAVITY HOUSING	2
1	B	BLACK	PBT-GF30	36WAY OUTER HOUSING	1
2390421-1	REV	COLOR	MATERIAL NO	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.ZHOU 27MAY2021	TE Connectivity		
		CHK T.DONG 27MAY2021			
		APVD J.ZONG 27MAY2021	NAME 36POS, HYB MCP 1.5K/2.8 REC HSG ASSY		
		PRODUCT SPEC 108-160374			
		APPLICATION SPEC 114-160565	SIZE A3 CAGE CODE 00779 DRAWING NO C-2390421 RESTRICTED TO		
		WEIGHT -			
RESTRICTED CUSTOMER		SCALE 1:1		SHEET 1 OF 1	REV B1

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 0.1	± 0.1
		1 PLC ± 0.01	± 0.01
		2 PLC ± 0.001	± 0.001
		3 PLC ± 0.0001	± 0.0001
		4 PLC $\pm$	$\pm$
MATERIAL SEE TABLE		FINISH -	-
		-	-