


A

B

C

D

E



技术参数 (SPECIFICATION):

温度范围 (TEMPERATURE RANGE): $-40 \sim +70^{\circ}\text{C}$

额定电压 (VOLTAGE RATING): 125V

额定电流 (CURRENT RATING): 1.5A

接触电阻 (CONTACT RESISTANCE): $\leq 30\text{m}\Omega$

绝缘电阻 (INSULATION RESISTANCE): $\geq 500\text{M}\Omega$

耐压 (DIELECTRIC STRENGTH): $500\text{V AC}/(50\text{HZ})/\text{Min}$

插拔力 (MATING AND UNMATING FORCE): $3 \sim 20\text{N}$

寿命 (DURABILITY): 750 CYCLES MIN

Table 1	
X	Terminal Plating
0	Au Fu" Plating
1	Au 1u" Plating
2	Au 2u" Plating
3	Au 3u" Plating
4	Au 6u" Plating
5	Au 10u" Plating
6	Au 15u" Plating
7	Au 30u" Plating

Material & Plating

Part NO.:
RCH563114-DD-X-XX

Table 2	
D	L LED/R LED
YG	YELLOW/GREEN
GY	GREEN/YELLOW
YY	YELLOW/YELLOW
GG	GREEN/GREEN
OO	OTHER/OTHER

Table 3	
XX	Material/Color
BB	PBT/BLACK
BW	PBT/WHITE
AB	PA/BLACK
AW	PA/WHITE
OO	OTHER/OTHER

6	外壳	H62	1	NI	
5	LED灯	树脂/FE	8	NI/AG	
4	插针	PHOSPHOR BRONZE	32	AU	
3	中分体	PA	2	BLACK	
2	右分体	PA	1	BLACK	
1	左分体	PA	1	BLACK	
序号	名称	材料	数量	镀层/颜色	备注

网络插座外形图

深圳市威电康精密科技有限公司

绘图:	日期:
审核:	日期:
核准:	日期:

一般公差		品名:			
30~	± 0.25	料号:	RJ45-1*4P带灯带弹		
10~30	± 0.20	型号:	RJ45	图号:	
~10	± 0.15	版本:	单位:mm	比例: 1:1	纸张: A4
角度:	$\pm 2^{\circ}$	页面:	1 of 1		

A/0	新出版发行				
版次	变更履历	变更单号	绘制	日期	核准
1	2	3			