







SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
2、Voltage Rating: 600V AC, DC
3、Temperatuer Range: -25℃~+85℃
4、Contact Resistance: 20mΩ Max
5、Insulation Resistance: 1000MΩ Min
6、Withstanding Voltang: 1500V AC/minute
7、Material:Wafer PA66, UL94V-2
PIN Brass Tin-plated

版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



PCB LAYOUT




PIN	尺寸 (mm)	
	A	B
-2*01A	---	5.40
-2*02A	4.20	9.60
-2*03A	8.40	13.80
-2*04A	12.60	18.00
-2*05A	16.80	22.20
-2*06A	21.00	26.40
-2*07A	25.20	30.60
-2*08A	29.40	34.80
-2*09A	33.60	39.00
-2*10A	37.80	43.20
-2*11A	42.00	47.40
-2*12A	46.20	51.60


GENERAL TOLERANCE		制 图 Mapping	张迎春 2022、12、08			料 号 PART NO.	A42002-2*nA	版本 REV.	A
X.±0.25	X.°±2°		审 核 Audit	钱岳生 2022、12、08			品 名 TITLE	5557双排直针 WAFER SMT TYPE	页 次 SHEET
.X±0.25	.X°±1°	核 准 Approved		张 名 2022、12、09			客户料号 CUTM. NO.		
.XX±0.15	.XX°±0.5°		单 位 Units	mm	比 例 SCALE	深圳市金航标电子有限公司			
.XXX±0.10	.XXX°±0.5°								

P位结构示意图


版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN




2*01A




2*02A




2*03A




2*04A




2*05A




2*06A




2*07A




2*08A




2*09A



2*10A



2*11A



2*12A

GENE RL TOLERANCE		制 图 Mapping	张迎春 2022、12、08	料 号 PART NO.	A42002-2*nA	版 本 REV.	A
X.±0.25	X.°±2°	审 核 Audit	钱岳生 2022、12、08	品 名 TITLE	5557双排直针 WAFER DIP TYPE	页 次 SHEET	2/2
.XX±0.15	.XX°±0.5°	核 准 Approved	张 名 2022、12、09	客户料号 CUTM. NO.			
.XXX±0.10	.XXX°±0.5°	单 位 Units	mm	比 例 SCALE			

深圳市金航标电子有限公司