






PCB LAYOUT

PIN	尺寸 (mm)	
	A	B
-02AW	4.20	9.60
-03AW	8.40	13.80
-04AW	12.6	18.00
-05AW	16.80	22.20
-06AW	21.00	26.40

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material:Wafer PA66, UL94V-2
PIN Brass Tin-plated

GENEERL TOLERANCE		制 图 Mapping	张迎春 2022、12、08	料 号 PART NO.	A42002-nAW	版 本 REV.	A
X.±0.25	X.°±2°	审 核 Audit	钱岳生 2022、12、08	品 名 TITLE	5557单排弯针 WAFER DIP TYPE	页 次 SHEET	1/1
.X±0.25	.X°±1°	核 准 Approved	张 名 2022、12、09	客户料号 CUTM. NO.	深圳市金航标电子有限公司		
.XX±0.15	.XX°±0.5°	单 位 Units	mm	比 例 SCALE			
.XXX±0.10	.XXX°±0.5°						