







版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer PA66, UL94V-2
PIN Brass Tin-plated

PIN	尺寸 (mm)	
	A	B
-02R	4.20	9.80
-03R	8.40	14.00
-04R	12.60	18.20
-05R	16.80	22.40
-06R	21.00	26.60

GENEERL TOLERANCE		制 图 Mapping	张迎春 2022、12、08			料 号 PART NO.	A42002-nR	版 本 REV.	A
X.±0.25	X.°±2°		钱岳生 2022、12、08			品 名 TITLE	5557单排母壳	页 次 SHEET	1/1
.X±0.25	.X°±1°	审 核 Audit	张 名 2022、12、09			客 户 料 号 CUTM. NO.			
.XX±0.15	.XX°±0.5°	核 准 Approved							
.XXX±0.10	.XXX°±0.5°	单 位 Units	mm	比 例 SCALE		深圳市金航标电子有限公司			