





版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN




SEC:C-C

SPECIFICATIONS

1. Current Rating: 7A AC, DC
2. Voltage Rating: 600V AC, DC
3. Temperatuer Range: -25°C ~ +85°C
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000MΩ Min
6. Withstanding Voltang: 1500V AC/minute
7. Material:Phosphoric bronze Tin-plated
8. Applicable Wire Sizes:AWG#20~26#



SEC:A-A



SEC:B-B

GENERL TOLERANCE		制图 Mapping	张迎春 2022、12、08		料号 PART NO.	A42001-RT	版本 REV.	A
X.±0.25	X.°±2°	审核 Audit	钱岳生 2022、12、08		品名 TITLE	5557公端	页次 SHEET	1/1
.X±0.25	.X°±1°	核 准 Approved	张名 2022、12、09		客户料号 CUTM. NO.			
.XX±0.15	.XX°±0.5°							
.XXX±0.10	.XXX°±0.5°	单位 Units	mm	比例 SCALE				

深圳市金航标电子有限公司