








PCB LAYOUT

PIN	尺寸 (mm)	
	A	B
-02A	4.20	9.60
-03A	8.40	13.80
-04A	12.6	18.00
-05A	16.80	22.20
-06A	21.00	26.40

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 600V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material:Wafer PA66, UL94V-2
PIN Brass Tin-plated

GENERAL TOLERANCE		制 图 Mapping	张迎春			料 号 PART NO.	A42002-nA	版 本 REV.	A
X $\pm$ 0.25	X $^{\circ}\pm 2^{\circ}$		2022、12、08				品 名 TITLE	5557单排直针 WAFER DIP TYPE	页 次 SHEET
.X $\pm$ 0.25	.X $^{\circ}\pm 1^{\circ}$	审 核 Audit	钱岳生			客户料号 CUTM. NO.			
.XX $\pm$ 0.15	.XX $^{\circ}\pm 0.5^{\circ}$		2022、12、08						
.XX $\pm$ 0.15	.XX $^{\circ}\pm 0.5^{\circ}$	核 准 Approved	张 名						
.XXX $\pm$ 0.10	.XXX $^{\circ}\pm 0.5^{\circ}$		2022、12、09						
		单 位 Units	mm	比 例 SCALE		深圳市金航标电子有限公司			