

PIN	尺寸 (mm)	
	A	B
-2*01R	---	5.40
-2*02R	4.20	9.80
-2*03R	8.40	14.00
-2*04R	12.60	18.20
-2*05R	16.80	22.40
-2*06R	21.00	26.60
-2*07R	25.20	30.80
-2*08R	29.40	35.00
-2*09R	33.60	39.20
-2*10R	37.80	43.40
-2*11R	42.00	47.60
-2*12R	46.20	51.80


SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
 - 2、Voltage Rating: 600V AC, DC
 - 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
 - 4、Contact Resistance: $20\text{m}\Omega$ Max
 - 5、Insulation Resistance: $1000\text{M}\Omega$ Min
 - 6、Withstanding Voltang: 15000V AC/minute
 - 7、Material:PA66, UL94V-2


GENERAL TOLERANCE		制图 Mapping	张迎春		料号 PART NO.	A42002-2*nR		版本 REV.	A
X.±0.25	X.°±2°		2022、12、08			5557双排母壳			
X.±0.25	X.°±1°	审核 Audit	钱岳生		品名 TITLE	5557双排母壳		页次 SHEET	1/2
			2022、12、08			5557双排母壳			
XX.±0.15	XX.°±0.5°	核准 Approved	张名		客户料号 CUTM. NO.	5557双排母壳		深圳市金航标电子有限公司	
			2022、12、09			5557双排母壳			
XXX.±0.10	XXX.°±0.5°	单位 Units	mm	比例 SCALE		5557双排母壳		深圳市金航标电子有限公司	

1	2	3	4	5	6	7	8	9		
						版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN


P位结构示意图




2*01R




2*02R




2*03R




2*04R




2*05R




2*06R




2*07R




2*08R




2*09R



2*10R



2*11R



2*12R

GENERAL TOLERANCE	制图 Mapping	张迎春 2022、12、08	料号 PART NO.	A42002-2*nR	版本 REV.	A
X. \pm 0.25	X. \pm 2°	审核 Audit	钱岳生 2022、12、08	品名 TITLE	5557双排母壳	页次 SHEET
.X \pm 0.25	.X \pm 1°	核准 Approved	张名 2022、12、09	客户料号 CUTM. NO.		2/2
.XX \pm 0.15	.XX \pm 0.5°					
.XXX \pm 0.10	.XXX \pm 0.5°	单位 Units	mm	比例 SCALE		

深圳市金航标电子有限公司