






版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



SPECIFICATIONS

1、Current Rating: 7A AC, DC

2、Voltage Rating: 600V AC, DC

3、Temperatuer Range: -25℃~+85℃

4、Contact Resistance: 20mΩ Max

5、Insulation Resistance: 1000MΩ Min

6、Withstanding Voltang: 1500V AC/minute

7、Material:Wafer PA66,UL94V-2


PIN Brass Tin-plated

PIN	尺寸 (mm)	
	A	B
-2*01P	---	5.60
-2*02P	4.20	9.80
-2*03P	8.40	14.00
-2*04P	12.60	18.20
-2*05P	16.80	22.40
-2*06P	21.00	26.60
-2*07P	25.20	30.80
-2*08P	29.40	35.00
-2*09P	33.60	39.20
-2*10P	37.80	43.40
-2*11P	42.00	47.60
-2*12P	46.20	52.30


GENERL TOLERANCE		制 图 Mapping	张迎春 2022、12、08			料 号 PART NO.	A42002-2*nP	版 本 REV.	A
X.±0.25	X.°±2°		审 核 Audit	钱岳生 2022、12、08			品 名 TITLE	5557双排公壳	页 次 SHEET
.X±0.25	.X°±1°	核 准 Approved		张 名 2022、12、09			客户料号 CUTM. NO.		
.XX±0.15	.XX°±0.5°		深 圳 市 金 航 标 电 子 有 限 公 司						
.XXX±0.10	.XXX°±0.5°	单 位 Units				mm	比 例 SCALE		

P位结构示意图


版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN




2*01P




2*02P




2*03P




2*04P




2*05P




2*06P




2*07P




2*08P




2*09P



2*10P



2*11P



2*12P

GENERAL TOLERANCE		制 图 Mapping	张迎春 2022、12、08			料 号 PART NO.	A42002-2*nP	版 本 REV.	A
X.±0.25	X.°±2°		审 核 Audit	钱岳生 2022、12、08			品 名 TITLE	5557双排公壳	页 次 SHEET
.X±0.25	.X°±1°	核 准 Approved		张 名 2022、12、09			客户料号 CUTM. NO.		
.XX±0.15	.XX°±0.5°		深圳市金航标电子有限公司						
.XXX±0.10	.XXX°±0.5°	单 位 Units						mm	比 例 SCALE