




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 5A AC, DC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage): 1500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.
7. Apply to gauge): AWG#20~#24.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	± 0.30	X.*	$\pm 5^{\circ}$	PART NO.	TITLE:
.XX	± 0.25	.X*	$\pm 1^{\circ}$	B3001-2DP2	MX3.0MM TERMINAL
.XXX	± 0.15			DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm			CHED: Olvia	
MATERILA	— — —			APPD: Ava	
FINISH	— — —				SCALE N:A
					SHEET 1/1