


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Technical Index:

- 1.Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
- 2.Rated voltage: 250V DC/AC(rms).
- 3.Rated current: 5A AC,DC.
- 4.Contact resistance: $\leq 20\text{m}\Omega$.
- 5.Dielectricwithstanding voltage): 1500V AC/minute.
- 6.Insulation resistance: $\geq 1000\text{M}\Omega$.
- 7.Apply to gauge): AWG#22~#28(O.D1.80mm Max).

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd					
X.X	±0.30	X.*	±5°	PART NO.	TITLE:		
.XX	±0.25	.X*	±1°	B4201-2DP2	WBM4.2MM TERMINAL		
.XXX	±0.15			DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm			CHED: Olvia		SCALE	SHEET
MATERILA	— — —			APPD: Ava		N:A	1/1