



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术指标:

1. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. 额定电压: 250V AC,DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 5A AC,DC.

型号	CKT	A	B
C300E22-B2P12	2*1	0.00	5.30
C300E22-B4P12	2*2	3.00	8.30
C300E22-B6P12	2*3	6.00	11.30
C300E22-B8P12	2*4	9.00	14.30
C300E22-B10P12	2*5	12.00	17.30
C300E22-B12P12	2*6	15.00	20.30
C300E22-B14P12	2*7	18.00	23.30
C300E22-B16P12	2*8	21.00	26.30
C300E22-B18P12	2*9	24.00	29.30
C300E22-B20P12	2*10	27.00	32.30
C300E22-B22P12	2*11	30.00	35.30
C300E22-B24P12	2*12	33.00	38.30

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO. C300E22-BXP12		TITLE: MX3.0MM HOUSING	
.XX ±0.25	X.* ±1°				
.XXX ±0.15		DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm				
MATERILA	— — —	CHED: Olivia		 SCALE N:A SHEET 1 / 1	
FINISH	— — —	APPD: Ava			

