








Technical Index:
 1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
 2. Rated voltage: 250V DC/AC(rms).
 3. Rated current: 3.0A.
 4. Contact resistance: $\leq 20\text{m}\Omega$.
 5. Withstanding voltage: 1000V AC/minute.
 6. Insulation resistance: $\geq 1000\text{M}\Omega$.


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
A254E1L1-2Y2P12	2	2.5	7.5
A254E1L1-2Y3P12	3	5.0	10.0
A254E1L1-2Y4P12	4	7.5	12.5
A254E1L1-2Y5P12	5	10.0	15.0
A254E1L1-2Y6P12	6	12.5	17.5
A254E1L1-2Y7P12	7	15.0	20.0
A254E1L1-2Y8P12	8	17.5	22.5
A254E1L1-2Y9P12	9	20.0	25.0
A254E1L1-2Y10P12	10	22.5	27.5
A254E1L1-2Y11P12	11	25.0	30.0
A254E1L1-2Y12P12	12	27.5	32.5
A254E1L1-2Y13P12	13	30.0	35.0
A254E1L1-2Y14P12	14	32.5	37.5
A254E1L1-2Y15P12	15	35.0	40.0
A254E1L1-2Y16P12	16	37.5	42.5
A254E1L1-2Y17P12	17	40.0	45.0



适用线路板(PCB LAYOUT)

序号	品名	材质
1	HA2.5 胶芯	PA66 UL94V-2 Beige
2	HA2.5 直针 端子	Copper Alloy/ Tin Plating

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X:±0.35	X.X':±3°	PART NO. A254E1L1-2YXP12	TITLE: Socket-type terminal Vertical plug		
X.XX:±0.25	X.XX':±2°				
X.XXX:±0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1