



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Technical Index:

- 1.Temperature range:−25℃~85℃.
- 2.Rated voltage:250V DC/AC(rms).
- 3.Rated current:5A AC,DC.
- 4.Contact resistance:≤20mΩ.
- 5.Dielectricwithstanding voltage):1500V AC/minute.
- 6.Insulation resistance:≥1000MΩ.
- 7.Apply to gauge):AWG#20~#24.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X	±0.30	X.*	±5°	PART NO. B3002-2DP2
.XX	±0.25	.X*	±1°	
.XXX	±0.15			DESIGN: Ethan
UNITS	mm			
MATERILA	— — —	CHED:	Olvia	TITLE: MX3.0MM TERMINAL
FINISH	— — —	APPD:	Ava	
				MANUFACTURE DWG
				SCALE N:A
				SHEET 1/1