



1. Configuration and Dimensions (Unit:m/m)



TYPE	A	B	C	D	E	F	G	H	I	J	K	Q'TY/Reel
ACM-4	9.2±0.3	6.0±0.3	5.0±0.3	1.4 Ref	1.0±0.1	2.54±0.2	5.7 Ref	2.0	1.2	9.5	2.54	1000

2. Electrical Schematics :



3. Electrical Spec.

Part Number	Turn Ratio	Inductance (uH) 1KHz,0.1V	LL (uH max)	Wistanding Voltage	DCR (AT 25℃) (Ω Max)	Primary pins
ACM-4N510	1:1± 5%	51±30%	0.5	AC500V/1mA /2S	0.16	1-2