


1. External Dimensions (Unit:m/m)



TYPE	A	B	C	D	E	Q'Ty/Reel
ANL322522	3.2±0.2	2.5±0.2	2.2±0.2	1.9±0.2	0.5Ref	2000

2. Part Number Code

ANL 322522 J 470
A B C D

A: Series Name Wire Wound Chip Inductors
 B: Dimensions(mm) 322522:3.2×2.5×2.2
 C: Tolerance J: ±5%
 D: Inductance 470=47uH

3. Electrical Characteristics

Part Number	Inductance (uH)	Tolerance	Q Min.	DCR (Ω) Max.	IDC (mA)Max.	SRF (MHz)Min.	L,Q Test Frequency (MHz)
ANL322522J470	47.0	±5%	30.0	7.0	60.0	15.0	2.52

4. Curve

Typical electrical characteristics inductance change vs.DC superposition characteristics

