




标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE



| No. of<br>Contacts | Dimension |      |      |
|--------------------|-----------|------|------|
|                    | A         | B    | C    |
| 2                  | 2.5       | 9.9  | 5.9  |
| 3                  | 5.0       | 12.4 | 8.4  |
| 4                  | 7.5       | 14.9 | 10.9 |
| 5                  | 10.0      | 17.4 | 13.4 |
| 6                  | 12.5      | 19.9 | 15.9 |
| 7                  | 15.0      | 22.4 | 18.4 |
| 8                  | 17.5      | 24.9 | 20.9 |
| 9                  | 20.0      | 27.4 | 23.4 |
| 10                 | 22.5      | 29.9 | 25.9 |
| 11                 | 25.0      | 32.4 | 28.4 |
| 12                 | 27.5      | 34.9 | 30.9 |
| 13                 | 30.0      | 37.4 | 33.4 |
| 14                 | 32.5      | 39.9 | 35.9 |
| 15                 | 35.0      | 42.4 | 38.4 |
| 16                 | 37.5      | 44.9 | 40.9 |



2PIN



3~5PIN



W/COVER CONSTRUCTION

## 技术要求:

额定电流: 3.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25°C~85°C

接触电阻: ≤0.01Ω



绝缘电阻: ≥1000MΩ

耐 压: 1000V/min

材 料:

塑胶 LCP 米色

金属 黄铜 镀锡



PCB LAYOUT

TOL.: ±0.05

|    |     |     |       |     |
|----|-----|-----|-------|-----|
| 2  | 插针  | 铜   | 镀锡    |     |
| 1  | 基座  | LCP | 米色    |     |
| 序号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

|                |            |
|----------------|------------|
| 品 名<br>TITLE   | 针座         |
| 料 号<br>PART NO | HCZ0040-13 |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 列  
SCALE

1:1

|          |        |
|----------|--------|
| X.±0.30  | X.±5°  |
| .X±0.25  | .X±3°  |
| .XX±0.20 | .XX±1° |

|                |        |
|----------------|--------|
| 单 位<br>UNIT    | MM     |
| 张 数<br>PART NO | 1 OF 1 |
| 版 本<br>REV     | A      |

|                |      |
|----------------|------|
| 制 图<br>DRAW    | AhYe |
| 审 核<br>CHECKED | 夏操云  |
| 批 准<br>APPROVE | 赵亮亮  |

