




标记
MARKECN编号/变更内容
ECN NO/DEFINITION修改
REVISE日期
DATE核准
APPROVE

芯数	A	B	C
2	2.0	8.0	4.8
3	4.0	10.0	6.8
4	6.0	12.0	8.8
5	8.0	14.0	10.8
6	10.0	16.0	12.8
7	12.0	18.0	14.8
8	14.0	20.0	16.8
9	16.0	22.0	18.8
10	18.0	24.0	20.8
11	20.0	26.0	22.8
12	22.0	28.0	24.8
13	24.0	30.0	26.8
14	26.0	32.0	28.8
15	28.0	34.0	30.8
16	30.0	36.0	32.8



技术要求:

额定电流: 2.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25℃~85℃

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ



耐压: 800V/min

材料:

塑胶 LCP, 米色

插针 黄铜, 镀锡

焊片 黄铜, 镀锡



PCB LAYOUT

2	插针	铜	镀锡	
1	基座	LCP	米色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名 TITLE	针座
料号 PART NO	HCZZ0398-3

GENERAL TOLERANCES
(UNLESS SPECIFIED)比列
SCALE

1:1



X.±0.30	X.±5°
.X±0.25	.X±3°
.XX±0.20	.XX±1°

单位 UNIT	MM
张数 PART NO	1 OF 1
版本 REV	A

制图 DRAW	AhYe
审核 CHECKED	夏操云
批准 APPROVE	赵亮亮

