





A
黑
红
绿

200mm

3mm

剥皮镀锡

线型：1007 22#



REV.	ECN	DESCRIPTION	MDF'D	DATE	
		新订图面			

PIN数	型号	尺寸 (mm)	
		A	B
2	MX3.96-2Y	3.96	8.52
3	MX3.96-3Y	7.92	12.48
4	MX3.96-4Y	11.88	16.44
5	MX3.96-5Y	15.84	20.40
6	MX3.96-6Y	19.80	24.36
7	MX3.96-7Y	23.76	28.32
8	MX3.96-8Y	27.72	32.28
9	MX3.96-9Y	31.68	36.24
10	MX3.96-10Y	35.64	40.20
11	MX3.96-11Y	39.60	44.16
12	MX3.96-12Y	43.56	48.12
13	MX3.96-13Y	47.52	52.08
14	MX3.96-14Y	51.48	56.04
15	MX3.96-15Y	55.44	60.00
16	MX3.96-16Y	59.40	63.96

技术要求

1. 温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. 额定电压 (Voltage rating): 250V. AC/DC
3. 额定电流 (Current rating): 4A
4. 接触电阻 (Contact resistance): $\leq 0.02 \Omega$
5. 绝缘电阻 (Insulation resistance): $\geq 1000\text{M}\Omega$
6. 耐压 (Withstand voltage): 1000V. AC/1分钟 (Minute)

 **韩下**[®] 深圳市韩下电子有限公司

页码 (SHEET)	1	单位 (UNIT): MM
版本 (REV)	A1	比例 (SCALE): 1:1
日期 (DATE)	2024.3.20	
设计 (DESIGN)	黄彬	未注公差 TOLERANCE UNSPECIFIED
审核 (CHECKED)	张伟	$> XX \pm 3$ $> X \pm 1$ 0.X ± 0.20 0.XX ± 0.15
核准 (APPROVED)	罗小春	