




REV.	ECN	DESCRIPTION	MDF'D	DATE
		新订图面		

PIN数	型号	尺寸 Size (mm)	
		A	B
2	SH1.0-2Y	1.0	4.95
3	SH1.0-3Y	2.0	5.95
4	SH1.0-4Y	3.0	6.95
5	SH1.0-5Y	4.0	7.95
6	SH1.0-6Y	5.0	8.95
7	SH1.0-7Y	6.0	9.95
8	SH1.0-8Y	7.0	10.95
9	SH1.0-9Y	8.0	11.95
10	SH1.0-10Y	9.0	12.95
11	SH1.0-11Y	10.0	13.95
12	SH1.0-12Y	11.0	14.95
13	SH1.0-13Y	12.0	15.95
14	SH1.0-14Y	13.0	16.95
15	SH1.0-15Y	14.0	17.95
16	SH1.0-16Y	15.0	18.95
17	SH1.0-17Y	16.0	19.95
18	SH1.0-18Y	17.0	20.95
19	SH1.0-19Y	18.0	21.95
20	SH1.0-20Y	19.0	22.95

- 技术要求:
- 标识清晰可见, 表面不得有划痕, 裂纹, 起泡, 污损, 毛刺等明显影响使用功能和接触性能的缺陷
 - 材料: 塑料PA66
 - 额定电流: 1.5A
 - 额定电压: 30V AC, DC
 - 温度范围: -25℃ to +85℃
 - 接触电阻: ≤0.02Ω
 - 绝缘电阻: ≥100MΩ
 - 适用线型: AWG#32 to #28
 - 耐电压: 250V AC/minute

 深圳市韩下电子有限公司	页码 (SHEET)	1	单位 (UNIT): MM
	版本 (REV)	A1	比例 (SCALE) 1:1
品名 (ITEM NO)	HX 1.0-4P DT 200mm 28AWG	日期 (DATE)	2024.3.20
料号 (PART NO)		设计 (DESIGN)	黄彬
图号 (DWG NO)		审核 (CHECKED)	张伟
		核准 (APPROVED)	罗小春
		未注公差 TOLERANCE UNSPECIFIED	
		> XX ±3 > X ±1 0.X ±0.20 0.XX ±0.15	