





REV.	ECN	DESCRIPTION		MDF'D	DATE
		新订图面			
		PIN数	型号	尺寸 (mm)	
			A B		
2	MX3.96-2Y	3.96	8.52		
3	MX3.96-3Y	7.92	12.48		
4	MX3.96-4Y	11.88	16.44		
5	MX3.96-5Y	15.84	20.40		
6	MX3.96-6Y	19.80	24.36		
7	MX3.96-7Y	23.76	28.32		
8	MX3.96-8Y	27.72	32.28		
9	MX3.96-9Y	31.68	36.24		
10	MX3.96-10Y	35.64	40.20		
11	MX3.96-11Y	39.60	44.16		
12	MX3.96-12Y	43.56	48.12		
13	MX3.96-13Y	47.52	52.08		
14	MX3.96-14Y	51.48	56.04		
15	MX3.96-15Y	55.44	60.00		
16	MX3.96-16Y	59.40	63.96		



线型：1007 22#



技术要求

- 温度范围 (Temperature range) : -25° c ~ +85° c
- 额定电压 (Voltage rating) : 250V. AC/DC
- 额定电流 (Current rating) : 4A
- 接触电阻 (Contact resistance) : ≤ 0.02 Ω
- 绝缘电阻 (Insulation resistance) ≥ 1000M Ω
- 耐压 (Withstand voltage) : 1000V. AC/1分钟 (Minute)

 **韩下**® 深圳市韩下电子有限公司

页码 (SHEET)	1	单位 (UNIT) : MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024. 3. 20	○ ⊙
设计 (DESIGN)	黄彬	未注公差 TOLERANCE UNSPECIFIED
审核 (CHECKED)	张伟	> XX ± 3 > X ± 1 0.X ± 0.20 0.XX ± 0.15
核准 (APPROVED)	罗小春	