





1	2	3	4	5
---	---	---	---	---



REV.	ECN	DESCRIPTION		MDF'D	DATE
		新订图面			
		PIN数	型号	尺寸 Size (mm)	
				A	B
2	SH1.0-2Y	1.0	4.95		
3	SH1.0-3Y	2.0	5.95		
4	SH1.0-4Y	3.0	6.95		
5	SH1.0-5Y	4.0	7.95		
6	SH1.0-6Y	5.0	8.95		
7	SH1.0-7Y	6.0	9.95		
8	SH1.0-8Y	7.0	10.95		
9	SH1.0-9Y	8.0	11.95		
10	SH1.0-10Y	9.0	12.95		
11	SH1.0-11Y	10.0	13.95		
12	SH1.0-12Y	11.0	14.95		
13	SH1.0-13Y	12.0	15.95		
14	SH1.0-14Y	13.0	16.95		
15	SH1.0-15Y	14.0	17.95		
16	SH1.0-16Y	15.0	18.95		
17	SH1.0-17Y	16.0	19.95		
18	SH1.0-18Y	17.0	20.95		
19	SH1.0-19Y	18.0	21.95		
20	SH1.0-20Y	19.0	22.95		

技术要求:

1. 标识清晰可见，表面不得有划痕，裂纹，起泡，污损，毛刺等明显影响使用功能和接触性能的缺陷
2. 材料：塑料PA66
3. 额定电压：30V AC, DC
4. 温度范围：-25°C to +85°C
5. 接触电阻： $\leq 0.02\Omega$
6. 绝缘电阻： $\geq 100M\Omega$
7. 适用线型：AWG#32 to #28
8. 耐电压：250V AC/minute



 **汉下**® 深圳市汉下电子有限公司

品名 (ITEM NO)	HX 1.0-5P DT 200mm 28AWG
料号 (PART NO)	
图号 (DWG NO)	

页码 (SHEET)	1	单位 (UNIT) : MM
版本 (REV)	A1	比例 (SCALE) 1:1
日期 (DATE)	2024.3.20	未注公差 TOLERANCE UNSPECIFIED
设计 (DESIGN)	黄彬	> XX ± 3
审核 (CHECKED)	张伟	> X ± 1
核准 (APPROVED)	罗小春	0.X ± 0.20
		0.XX ± 0.15

1	2	3	4	5
---	---	---	---	---