




蓝
白
黄
黑
红

线型：1007 22#

剥皮镀锡

REV.		ECN	DESCRIPTION		MDF'D	DATE
			新订图面			
PIN数	型号	尺寸 (mm)				
		A	B			
2	MX3.96-2Y	3.96	8.52			
3	MX3.96-3Y	7.92	12.48			
4	MX3.96-4Y	11.88	16.44			
5	MX3.96-5Y	15.84	20.40			
6	MX3.96-6Y	19.80	24.36			
7	MX3.96-7Y	23.76	28.32			
8	MX3.96-8Y	27.72	32.28			
9	MX3.96-9Y	31.68	36.24			
10	MX3.96-10Y	35.64	40.20			
11	MX3.96-11Y	39.60	44.16			
12	MX3.96-12Y	43.56	48.12			
13	MX3.96-13Y	47.52	52.08			
14	MX3.96-14Y	51.48	56.04			
15	MX3.96-15Y	55.44	60.00			
16	MX3.96-16Y	59.40	63.96			

技术要求

- 温度范围 (Temperature range): -25° c ~ +85° c
- 额定电压 (Voltage rating): 250V.AC / DC
- 额定电流 (Current rating): 4A
- 接触电阻 (Contact resistance): ≤ 0.02 Ω
- 绝缘电阻 (Insulation resistance) ≥ 1000M Ω
- 耐压 (Withstand voltage): 1000V.AC / 1分钟 (Minute)

 深圳市韩下电子有限公司	页码 (SHEET)	1	单位 (UNIT): MM
	版本 (REV)	A1	比例 (SCALE) 1:1
品名 (ITEM NO)	HX CH3.96-5P DT 200mm 22AWG	日期 (DATE)	2024.3.20
料号 (PART NO)		设计 (DESIGN)	黄彬
图号 (DWG NO)		审核 (CHECKED)	张伟
		核准 (APPROVED)	罗小春
		未注公差 TOLERANCE UNSPECIFIED	
		> XX	±3
		> X	±1
		0.X	±0.20
		0.XX	±0.15