








标 记  
MARKECN编号/变更内容  
ECN NO/DEFINITION修 改  
REVISE日 期  
DATE核 准  
APPROVE

| No. of<br>Contacts | DIM A | DIM B | DIM C |
|--------------------|-------|-------|-------|
| 2                  | 1.25  | 3.85  | 5.75  |
| 3                  | 2.50  | 5.10  | 7.00  |
| 4                  | 3.75  | 6.35  | 8.25  |
| 5                  | 5.00  | 7.60  | 9.50  |
| 6                  | 6.25  | 8.85  | 10.75 |
| 7                  | 7.50  | 10.10 | 12.00 |
| 8                  | 8.75  | 11.35 | 13.25 |
| 9                  | 10.00 | 12.60 | 14.50 |
| 10                 | 11.25 | 13.85 | 15.75 |
| 11                 | 12.50 | 15.10 | 17.00 |
| 12                 | 13.75 | 16.35 | 18.25 |
| 13                 | 15.00 | 17.60 | 19.50 |
| 14                 | 16.25 | 18.85 | 20.75 |
| 15                 | 17.50 | 20.10 | 22.00 |
| 16                 | 18.75 | 21.35 | 23.25 |



## 技术要求:

额定电流: 1.0A AC,DC  
(注: AWG32# 0.8)

额定电压: 50V AC

温度范围: -25°C~85°C

接触电阻: ≤0.02Ω






绝缘电阻: ≥100MΩ

耐 压: 500V AC/min

材 料:

塑胶 LCP,米色

金属 铜合金,镀锡



|    |    |     |       |    |
|----|----|-----|-------|----|
| 2  | 插针 | 铜   | 镀锡    |    |
| 1  | 基座 | LCP | 米色    |    |
| 序号 | 品名 | 材质  | 电镀/颜色 | 备注 |




深圳市虹成电子有限公司

|               |            |
|---------------|------------|
| 品名<br>TITLE   | 针座         |
| 料号<br>PART NO | HCZZ0014-8 |

GENERAL TOLERANCES  
(UNLESS SPECIFIED)比 例  
SCALE

1:1



|          |        |
|----------|--------|
| X.±0.30  | X.±5°  |
| .X±0.25  | .X±3°  |
| .XX±0.20 | .XX±1° |

|               |        |
|---------------|--------|
| 单位<br>UNIT    | MM     |
| 张数<br>PART NO | 1 OF 1 |
| 版本<br>REV     | A      |

|                |      |
|----------------|------|
| 制 图<br>DRAW    | AhYe |
| 审 核<br>CHECKED | 夏操云  |
| 批 准<br>APPROVE | 赵亮亮  |

