




REV.	ECN	DESCRIPTION	MDF'D	DATE
		新订图面		
		PIN数	型号	尺寸 (mm)
				A B
		2	MX3.96-2Y	3.96 8.52
		3	MX3.96-3Y	7.92 12.48
		4	MX3.96-4Y	11.88 16.44
		5	MX3.96-5Y	15.84 20.40
		6	MX3.96-6Y	19.80 24.36
		7	MX3.96-7Y	23.76 28.32
		8	MX3.96-8Y	27.72 32.28
		9	MX3.96-9Y	31.68 36.24
		10	MX3.96-10Y	35.64 40.20
		11	MX3.96-11Y	39.60 44.16
		12	MX3.96-12Y	43.56 48.12
		13	MX3.96-13Y	47.52 52.08
		14	MX3.96-14Y	51.48 56.04
		15	MX3.96-15Y	55.44 60.00
		16	MX3.96-16Y	59.40 63.96

技术要求

1. 温度范围 (Temperature range): -25° c ~ +85° c
2. 额定电压 (Voltage rating): 250V.AC / DC
3. 额定电流 (Current rating): 4A
4. 接触电阻 (Contact resistance): ≤ 0.02 Ω
5. 绝缘电阻 (Insulation resistance) ≥ 1000M Ω
6. 耐压 (Withstand voltage): 1000V.AC / 1分钟 (Minute)

 韩下® 深圳市韩下电子有限公司	页码 (SHEET)	1	单位 (UNIT): MM
	版本 (REV)	A1	比例 (SCALE) 1:1
品名 (ITEM NO)	HX CH3.96-4P DT 200mm 22AWG	日期 (DATE)	2024.3.20
料号 (PART NO)		设计 (DESIGN)	黄彬
图号 (DWG NO)		审核 (CHECKED)	张伟
		核准 (APPROVED)	罗小春

未注公差 TOLERANCE UNSPECIFIED	
> XX	±3
> X	±1
0.X	±0.20
0.XX	±0.15