

标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

A

B







C

D

E

F

G

PCB LAYOUT
TOL.: ±0.05

No. of Contacts	Dimension		
	A	B	C
2	2.5	9.9	5.9
3	5.0	12.4	8.4
4	7.5	14.9	10.9
5	10.0	17.4	13.4
6	12.5	19.9	15.9
7	15.0	22.4	18.4
8	17.5	24.9	20.9
9	20.0	27.4	23.4
10	22.5	29.9	25.9
11	25.0	32.4	28.4
12	27.5	34.9	30.9
13	30.0	37.4	33.4
14	32.5	39.9	35.9
15	35.0	42.4	38.4
16	37.5	44.9	40.9

A

B

C

D

E

F

G

技术要求:

额定电流: 3.0A AC,DC

额定电压: 250V AC,DC

温度范围: -25°C~85°C

接触电阻: ≤0.01Ω

绝缘电阻: ≥1000MΩ


耐 压: 1000V/min

材 料:

塑胶 LCP 米色

金属 黄铜 镀锡

2	插针	铜	镀锡	
1	基座	LCP	米色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	针座	
			料 号 PART NO	HCZZ0520-8	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.±0.30	X.±5°	单 位 UNIT	MM	制 图 DRAW	AhYe
.X±0.25	.X±3°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
.XX±0.20	.XX±1°	版 本 REV	A	批 准 APPROVE	赵亮亮

